PD40-05 series

- Mid-IR PD Series
- Max. Sensitivity: 2.3 3.85 μm
- Sensitive Area Diameter: Ø 0.5 mm





Description

PD40-05 series are fabricated from narrow band-gap InAsSb/InAsSbP-based heterostructures lattice matched to InAs substrate. The maximum sensitivity wavelength is specified with $2.3-3.85~\mu m$ and a cut-off wavelength at 4.1 μm . The photodiode chip has a photosensitive area of Ø 0.5 mm and can be mounted into different options of packages. You can choose between TO-can, with additional parabolic reflector (R), window (W), containing thermoelectric cooler and thermoresistor (T), and as aluminum tube with built-in preamplifier.

Maximum Ratings

Davameter	Symbol	Val	Heit	
Parameter		Min.	Max.	Unit
Operating Temperature *1	TCASE	-60	+ 90	°C
Storage Temperature *1	T _{STG}	-60	+ 90	°C
Lead Solder Temperature *2	T_{SLD}		+ 180	°C

^{*1} Temperature range may vary for different packaging types.

Photodiode Characteristics (TCASE=25°C)


Parameter	Cumbal	Conditions	Values			I Incid
Farameter	Symbol		Min.	Тур.	Max.	Unit
Sensitive Area Diameter	D			0.5		mm
Cut-off Wavelength (at 10%)	λ_{cut}			4.1		μm
Max. Sensitivity Wavelength (at 80%)	λ_P		2.3		3.85	μm
Reverse Voltage	V _R				0.1	V
Dark Current	I D	V _R =0.1V		1.2	1.8	mA
Shunt Resistance	RsH	V _R =10mV	30	50		Ω
Capacitance	С	$V_R=10mV$		-		pF
Sensitivity	S	λ=3.8μm	1.1	1.2		A/W
Noise Equivalent Power	NEP	λ=3.8μm		1.5*10 ⁻¹¹	2.1*10 ⁻¹¹	W/\sqrt{Hz}
Detectivity	D*	λ=3.8μm	2.0*109	2.8*10 ⁹		$cm\cdot \sqrt{Hz}\cdot W^{-1}$


Package Options


Part Number	Description
PD40-05	TO-18 with cap without glass window
PD40-05R	TO-18 with parabolic reflector without glass window
PD40-05RW	TO-18 with parabolic reflector with glass window
PD40-05TW	TO-5 with built-in thermocooler and thermoresistor, covered by cap with glass window
PD40-05TRW	TO-5 with built-in thermocooler and thermoresistor, covered by parabolic reflector with glass window
PD40-05R-AMP	PD with built-in preamplifier; TO-18 with parabolic reflector without window in an aluminum tube
PD40-05RW-AMP	PD with built-in preamplifier; TO-18 with parabolic reflector with window in an aluminum tube


^{*2} must be completed within 5 seconds


Performance Characteristics













Recommended Modes of Photodiode Operation






We recommend using **photovoltaic mode** when the PD is not used in reverse bias. Use photoconductive mode (mode with reverse bias) with caution!

Important Cautions:

- Check your connection circuits before turning on the PD.
- Mind the PD polarity: PD anode is marked with a RED dot.
- DO NOT connect the PD to the multimeter.

Outline Dimensions



All Dimensions in mm




ROITHNER LASERTECHNIK GmbH

WIEDNER HAUPTSTRASSE 76 IO40 VIENNA AUSTRIA TEL. +43 I 586 52 43 -0, FAX. -44 OFFICE@ROITHNER-LASER.COM



PD40-05R


TO-18 with parabolic reflector without glass window



All Dimensions in mm

PD40-05RW

TO-18 with parabolic reflector with glass window




Lead	Description
PIN 1	PD Cathode
PIN 2	PD Anode
PIN 3	Ground

All Dimensions in mm

PD40-05TW

TO-5 with built-in thermocooler and thermoresistor, covered by cap with glass window




Lead	Description
PIN 1	TEC +
PIN 2	PD Anode
PIN 3	PD Cathode
PIN 4	Thermistor
PIN 5	Thermistor
PIN 6	TEC -

All Dimensions in mm




PD40-05TRW TO-5 with built-in thermocooler and thermoresistor, covered by parabolic reflector with glass window



All Dimensions in mm

PD40-05-AMP

PD with built-in preamplifier; TO-18 with parabolic reflector without window in an aluminum tube



All Dimensions in mm


Power input voltage: +5 V, stabilized **Connections:**

The output of PD with a built-in preamplifier has four wires:

- "+" power input (to the "+5V" of the power output terminal block of the synchronous detector);
- "ground" power input (to the "0V" of the power output terminal block of the synchronous detector);
- "ground" output photodiode signal (to the "0V" of the signal input terminal block of the synchronous detector);
- "+" output photodiode signal (to the "IN" of the signal input terminal block of the synchronous detector).

For the proper connection mind the colors of the wires pointed in the technical data provided with the photodiode.

PD40-05RW-AMP PD with built-in preamplifier; TO-18 with parabolic reflector with window in an aluminum tube



All Dimensions in mm

Power input voltage: +5 V, stabilized **Connections:**

The output of PD with a built-in preamplifier has four wires:

- "+" power input (to the "+5V" of the power output terminal block of the synchronous detector);
- "ground" power input (to the "0V" of the power output terminal block of the synchronous detector);
- "ground" output photodiode signal (to the "0V" of the signal input terminal block of the synchronous detector);
- "+" output photodiode signal (to the "IN" of the signal input terminal block of the synchronous detector).

For the proper connection mind the colors of the wires pointed in the technical data provided with the photodiode.

Precautions

Soldering:

- Do avoid overheating of the PD
- Do avoid electrostatic discharge (ESD)
- Do avoid mechanical stress, shock, and vibration
- Do only use non-corrosive flux
- Do not apply current to the LED until it has cooled down to room temperature after soldering

Static Electricity:

PDs are sensitive to electrostatic discharge (ESD). Precautions against ESD must be taken when handling or operating these PDs. Surge voltage or electrostatic discharge can result in complete failure of the device.



© All Rights Reserved

The above specifications are for reference purpose only and subjected to change without prior notice